

## Screen Prep™ Presaturated Wipe

Product# CSP20

### Product Description

Screen Prep Presaturated Wipes are a convenient cleaning and static control system for use on monitor screens. This two part system is excellent for use on computer display screens, scope and dial faces, and glass and plastic surfaces of instruments. These highly effective cleaning wipes are safe on plastics and are ideal for cleaning sensitive surfaces. Screen Prep provides a static-dissipative treatment to the surface to control static-generated contamination. Screen Prep removes dust, fingerprint oils and other vision-inhibiting contaminants, and leaves no residue.

Screen Prep Presaturated Wipes contain isopropyl alcohol and an anti-static agent.

- Plastic Safe
- Leaves No Residue
- Nonabrasive
- Static-dissipative
- Upper Ozone Safe; CFC/HCFC Free

### Typical Applications

Screen Prep cleans:

- Computer monitors
- Display screens
- Scope and dial faces
- Instrument readouts
- Equipment glass & plastic surfaces



### Typical Product Data and Physical Properties

Solubility in Water:	Soluble
Specific Gravity:	0.78
Evaporation Rate: (ether =1)	<1
Appearance:	Clear, colorless liquid
Flash Point (TCC):	165° F (73.9°C)
Percent Volatile	100%
Shelflife	2 years
RoHS Compliant	Yes

## Screen Prep™ Presaturated Wipe

**Product# CSP20**

### Compatibility

Screen Prep Presaturated Wipes are generally compatible with most plastics, glass and metals. Compatibility must be checked with all antiglare coatings. As with any chemical product, component compatibility must be determined on a non-critical area prior to use.

Material	Compatibility
Aluminum	Excellent
Buna-N	Excelent
CPVC	Excellent
Epoxy	Excellent
Neoprene	Excellent
Noryl®	Excellent
Phenolic	Excellent
Cross-Linked PE	Excellent
Polycarbonate	Excellent
Polypropylene	Excellent
Polystyrene	Excellent
PVC	Excellent
Teflon™	Excellent
Tygon™	Excellent
Viton™	Excellent

### Usage Instructions

*For industrial use only. Read SDS carefully prior to use.*  
Remove premoistened pad from packet #1 and lightly wipe away any dust or contaminants from surfaces. Remove dry wipe from packet #2 and wipe surface dry.

### Availability

CSP20 25 twin packs:  
Packet #1 contains 3" x 4" premoistened pad  
Packet #2 contains 4" x 6" dry wipe

### Environmental Impact Data

CFC	0.0%
HCFC	0.0%
CL Solv.	0.0%
VOC	25
HFC	0.0%
ODP	0.0

CFC, HCFC, CL. SOLV., VOC, and HFC numbers shown are the content by weight. Ozone depletion potential (ODP) is determined in accordance with the Montreal Protocol and U.S. Clean Air Act of 1990. The ODP of this product is zero.

### Technical and Application Assistance

Chemtronics provides a technical hotline to answer your technical and application related questions.  
The toll free number is: 1-800-TECH-401.

### Note:

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. CHEMTRONICS does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.